
## **ASSEMtech Europe Ltd**

## PRODUCT DATA SHEET



## **SPECIFICATION**

CONTACT FORM/STYLE		C/Changover	
SWITCHING VOLTAGE	Max. Vac	150	
SWITCHING CURRENT	Max. A	1.0	
SWITCHING CAPACITY (RESISTIVE)	Max. VA	20	
CONTACT RESISTANCE	Max. $m\Omega$	100	
SWITCHING DISTANCE	Min. mm	8.0	
OPERATING TEMPERATURE	Deg. °C	-20° + 70°	
STORAGE TEMPERATURE	Deg. °C	-25° + 70°	
CASE MATERIAL		Polystyrene	

PRODUCT GROUP TSS127/1

## **RECTANGULAR MAGNETIC PROXIMITY SWITCHES**

PART NUMBER PSC 150/30

Rev. No.	Revision Note	Date	Signature
A	FIRST ISSUE		



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.

BS5750/ISO 9000 Reg. No. FM 21080