

MRI20NA



Rated Impedance	Ω	8;16;32;50;150
Rated Power	W	0.25
Max Power	W	0.5
Resonance Frequency(F_0)	Hz	600
Rated Freq. Range	Hz	200-5000
Sound Pressure Level	dB	87 \pm 2;84 \pm 2;82 \pm 2
Crust		Iron
Height	mm	

