



RE436-LF

- Epoxy fibre-glass FR4 0.80 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Sn
- SMD hole spacing 1.27 x 1.27 mm
- 40 x 60 soldering pads 1.00 x 1.00 mm
- Hole diameter 0.35 mm
- 2 grids 2.54 x 2.54 mm (1/20") 17 x 32 and 18 x 32 soldering pads 2.00 x 2.00 mm
- Hole diameter 1.00 mm
- Connector 32/64/96-channel DIN 41612 type C
- Size 100 x 160 mm