



RE437-LF

- Epoxy fibre-glass FR4 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Sn
- SMD hole spacing 1.27 x 1.27 mm
- 108 x 69 soldering pads 1.00 x 1.00 mm (7452 soldering pads)
- 4 potential strips
- Connector 32/64/96-channel DIN 41612 type C
- Size 100 x 160 mm