



**Product:** [8918](#)

Lead Wire, #18 Str TC, PVC Ins, AWM 1015 AWM 1230

[Request Sample](#)

**Product Description**

Low Temp Plastic Lead Wire, 18AWG (16x30) Tinned Copper, PVC Insulation, AWM 1015 AWM 1230 CSA TYPE TEW JQA-F 600V 105C

**Technical Specifications**

**Product Overview**

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances, machine tool wire
------------------------	--

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
18	16x30	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness	Min. Average Wall Thickness
PVC - Polyvinyl Chloride	0.11 in	0.033 in	0.03 in

**Electrical Characteristics**

**Conductor DCR**

<b>Nominal Conductor DCR</b>
6.5 Ohm/1000ft

**Current**

Element	Max. Recommended Current [A]
Single conductor in free air @ 30C ambient	Single conductor in free air @ 30°C: 20 A

**Voltage**

<b>UL Voltage Rating</b>
600 V RMS

**Temperature Range**

UL Temp Rating:	105°C
-----------------	-------

**Mechanical Characteristics**

Bulk Cable Weight:	10 lbs/1000ft
--------------------	---------------

**Standards**

NEC Articles:	Article 310
NEC/(UL) Compliance:	MTW
UL AWM Style Compliance:	UL AWM Styles 1015, 1230
CSA Rating:	600 V, 105°C
CSA AWM Compliance:	CSA AWM I A/B

CSA Type:	AWM I A/B or TEW
-----------	------------------

### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-07-01
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

### Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	600 V RMS

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Part Number

#### Variants

Item #	Color	Putup Type	Length	UPC
8918 010100	Black	Reel	100 ft	612825219989
8918 0101000	Black	Reel	1,000 ft	612825219996
8918 0105000	Black	Reel	5,000 ft	612825220008
8918 013100	Blue, Dark	Reel	100 ft	612825220060
8918 0131000	Blue, Dark	Reel	1,000 ft	612825220077
8918 0135000	Blue, Dark	Reel	5,000 ft	612825220084
8918 001100	Brown	Reel	100 ft	612825219606
8918 0011000	Brown	Reel	1,000 ft	612825219613
8918 0081000	Gray	Reel	1,000 ft	612825219866
8918 0085000	Gray	Reel	5,000 ft	612825219873
8918 005100	Green, Dark	Reel	100 ft	612825219804
8918 0051000	Green, Dark	Reel	1,000 ft	612825219811
8918 0055000	Green, Dark	Reel	5,000 ft	
8918 189100	Green, Yellow Stripe	Reel	100 ft	612825220107
8918 1891000	Green, Yellow Stripe	Reel	1,000 ft	612825348030
8918 003100	Orange	Reel	100 ft	612825219699
8918 0031000	Orange	Reel	1,000 ft	612825219705
8918 002100	Red	Reel	100 ft	612825219637
8918 0021000	Red	Reel	1,000 ft	612825219644
8918 0025000	Red	Reel	5,000 ft	612825219651
8918 0071000	Violet	Reel	1,000 ft	612825219842
8918 009100	White	Reel	100 ft	612825219903
8918 0091000	White	Reel	1,000 ft	612825219910
8918 0095000	White	Reel	5,000 ft	612825219927
8918 004100	Yellow	Reel	100 ft	612825219743
8918 0041000	Yellow	Reel	1,000 ft	612825219750
8918 0045000	Yellow	Reel	5,000 ft	612825219767

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	P - STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M= FOR 1 OR 2 STRIPES. 10,000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL, WITH A MINIMUM LENGTH OF 100'.
Footnote:	A - STOCKED STRIPE COLORS.

## History

Update and Revision:	Revision Number: 0.299 Revision Date: 07-26-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Belden Wire & Cable:

[8918 0131000](#) [8918 0011000](#) [8918 0021000](#) [8918 0081000](#) [8918 0071000](#) [8918 001100](#) [8918 0051000](#) [8918 002100](#) [8918 0091000](#) [8918 009100](#) [8918 0101000](#) [8918 1891000](#) [8918 189100](#) [8918 0031000](#) [8918 013100](#)  
[8918 004100](#) [8918 010100](#) [8918 005100](#) [8918 0041000](#) [8918 003100](#) [8918 0085000](#) [8918 0095000](#) [8918 0045000](#)  
[8918 0055000](#) [8918 0105000](#) [8918 0025000](#) [8918 0135000](#)