



GM-5218

Order No.: 23.4390

Price upon request

PRODUCTINFOS

Electret gooseneck microphones

- Supercardioid polar pattern
- Excellent sound with a very high speech intelligibility
- Minimum susceptibility to acoustic feedback
- Solid and high-quality workmanship to ensure a long service life
- Gooseneck with integrated 3-pole XLR plug
- Operation via external phantom power or microphone base ST-5030

TECHNICAL SPECIFICATIONS

GM-5218

Type	gooseneck microphone
Transmission method	cable
Polar pattern	supercardioid
System	back electret

GM-5218

Audio frequency range	80-18,000 Hz
Nominal impedance	220 Ω
Sensitivity	16 mV/Pa
Max. sound pressure	125 dB
Power supply	DC 48 V phantom power
Admiss. ambient temp.	0-40 °C
Dimensions	605 mm
Weight	185 g
Connection	XLR, bal.