


PRODUCT NUMBER: 897-43-005-00-100001



DESCRIPTION

USB Connector
 Mini-B
 USB 2.0
 Rows: Single Row (1)
 Clip Grid: 00
 Pin Window Pattern 100
 Plating Code: 43
 Shell: 200 μ" Tin (matte finish) over 100 μ" Nickel
 Inner Contact: 30 μ" Gold over 50 μ" Nickel
 Insulator Pin Clip Type: 001
 Mounting Type: Surface Mount
 Packaging: Tape & Reel, 13" (330 mm) Reel
 Insulator Information:
 High Temperature

# Pins	Qty Reel	ROHS Compliant
--------	----------	----------------

5

700



STANDARD TOLERANCES ON PCB TERMINAL PINS & RECEPTACLES

Diameters +/- .002"
 Lengths +/- .005"
 Angles +/- 2°

STANDARD TOLERANCES ON SPRING-LOADED PINS

Diameters +/- .002"
 Lengths +/- .006"
 Angles +/- 2°

ADDITIONAL NOTES & SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

© 2021 Mill-Max Mfg. Corp.
 190 Pine Hollow Rd, Oyster Bay, NY 11771, USA
 Phone: 516.922.6000