



**CONNECTORS**

**AUTOMOTIVE CONNECTOR CAPS & COVERS**



✓ Active

TE CONNECTIVITY (TE)

## 40W MQS COVER ASSY (15D)

MQS

953122-1

TE Internal Number: 953122-1

EU RoHS Compliant

EU ELV Compliant

**Connector System** Wire-to-Board, Wire-to-Component

**Accessory Type** Cover Assembly

**Cable Exit Angle** 15

**Strain Relief** With

**Color** Black

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### DOCUMENTATION

Product Drawings

#### **ASSEMBLY COVER 40 WAY MQS CABLE-LOCKING AT 15 DEG.**

PDF

**English**

CAD Files

#### **Customer View Model**

3D\_IGS.ZIP

**English**

#### **Customer View Model**

3D\_STP.ZIP

**English**

#### **Customer View Model**

2D\_DXF.ZIP

**English**

### 3D PDF

PDF

**English**

---

Product Specifications

Product Specification

### PORTE-CLIPS MQS 40 VOIES

PDF

**French**

---

Instruction Sheets

Instruction Sheet (non U.S.)

### RECOMMANDATIONS GENERALES D'UTILISATION PORTE-CLIPS 40 VOIES MQS

PDF

**French**

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Connector System** Wire-to-Board, Wire-to-Component

**Accessory Type** Cover Assembly

**Strain Relief** With

**Sealed** No

---

Configuration Features

**Number of Positions** 40

---

Body Features

**Cable Exit Angle** 15

**Color** Black

**Material** PBT GF

---

Usage Conditions

**Operating Temperature (Max) (°C)** 85, 90, 100

**Operating Temperature (Max) (°F)** 185, 194, 212

**Operating Temperature Range** -40 – 100 °C [ -40 – 212 °F ]

---

Packaging Features

**Packaging Method** Box

**Packaging Quantity** 180

Statement of Compliance

**Statement of Compliance**

PDF