

## Datasheet

Art.No. 96.051.4053.1

Female connector with strain relief RST20I5S B1 ZR1 SW

Connector RST20i5, 5 pole, female, screw connection, 250/400V, 20A, for cable diameters 6-10 mm, color of coding: black, color of housing: black



Art.No.	96.051.4053.1
EAN	4015573861824
Order unit	1 pieces

## Approvals



## Technical data

### General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

### Connection Data

Connection cross section solid	4 mm <sup>2</sup>
Connection cross section stranded	4 mm <sup>2</sup>
Terminations per pole	1

### Model

Model	female
Number of poles	5
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

### Material

Housing material	Polyamide
------------------	-----------

Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

**Dimensions**

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

