

# CERAMIC SMD CRYSTAL



**ABM3C**

RoHS/RoHS II Compliant

5.0 x 3.2 x 1.3mm

ABM3C Series products with the Date Code/Traceability Code marking ending in "X" are Glass-Sealed and the following RoHS Exemption applies: Pb in Glass, exemption 7C-I per RoHS II Directive 2011/65/EU Annex

ABM3C Series products with the Date Code/Traceability Code marking ending in "C" and "F" are Seam-Sealed and are Pb-Free.

Moisture Sensitivity Level – MSL – N/A (The ABM3C Series is a Hermetically Sealed device and not moisture sensitive)

➤ **FEATURES:**

- Low height; suitable for thin equipment.
- New seam sealed package available (code "C")
- Tight tolerance and stability available.
- Suitable for RoHS compliant reflow profile



➤ **APPLICATIONS:**

- High density applications.
- Modems, communication and test equipment.
- PCMCIA, Wireless applications

➤ **STANDARD SPECIFICATIONS:**

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	10.000		50.000	MHz	Fundamental
Operation Mode	Fundamental				
Operating Temperature	-10		+70	°C	See options
Storage Temperature	-40		+90	°C	
Frequency Tolerance @+25°C	-50		+50	ppm	See options
Frequency Stability over the Operating Temperature ( ref. to +25°C)	-50		+50	ppm	See options
Equivalent series resistance (R1)			60	Ω	10.000 – 15.999MHz
			50		16.000 – 50.000MHz
Shunt capacitance (C0)			7	pF	
Load capacitance (CL)		18		pF	Standard (See options if other than STD)
Drive Level		10	100	μW	
Aging	-5		+5	ppm	@25°C±3°C First year
Insulation Resistance	500			MΩ	@ 100Vdc ± 15V

➤ **OPTIONS & PART IDENTIFICATION:** (Left blank if standard)



# CERAMIC SMD CRYSTAL


**ABM3C**

RoHS/RoHS II Compliant



5.0 x 3.2 x 1.3mm

## OUTLINE DRAWING:




### Sealing Method :

Glass Sealing for parts with Traceability Code ending in "X"  
Seam Sealing for parts with Traceability Code ending in "C" and "F"


**Dimensions: inches (mm)**

## REFLOW PROFILE:



## TAPE & REEL:

1000pcs/reel



**Dimensions: mm**

**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 07.31.14**

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)