






Stäubli recommended Crimping pliers and crimping inserts

	Order No.	Type	For conductor cross section	Crimp form	Tractive system		Operating instructions ²⁾
					Hand	Hand-Hydraulic	
 2	18.3700	BEKU Apparatebau M-PZ13	6 mm ² – 25 mm ²	Hexagonal	x		 MA224
 3	18.3710	Elpress M-PZ-T2600	10 mm ² – 95 mm ²	Hexagonal	x		 MA226

Inserts

				Sizes of crimp sleeves for conductor class 6 ³⁾			
Conductor cross section		Crimping pliers	Order No.	Insert			X = Control dimension
mm ²	AWG				Ø A mm	Ø B mm	
6	8	2	18.3701	MES-PZ-TB5/6	4	6	–
10	6	2	18.3702	MES-PZ-TB8/10	5	8	6.3
16	4	2	18.3703	MES-PZ-TB9/16	6	9	7.3
25	2	2	18.3704	MES-PZ-TB11/25	8	11	8.8
35	1	3	18.3712	TB9-13 (KRF)	9	13	10.2
50	1/0	3	18.3713	TB11-14,5 (KRF)	11	14.5	11.4