

PROFIBUS®-PA, *eurofast*® Field Wireable Connectors

- Screw Terminals Accept up to 18 AWG Conductors



| Housing | Part Number          | Specs  | Application  | Pinouts       |
|---------|----------------------|--|--|---------------|
|         | <b>BS 8141-0/PG9</b> | PBT, Black<br>PG 7 cable gland,<br>accepts 4-8 mm cable diameter<br>85°C<br>125 V, 4 A | Mates with standard key<br>4-pin <i>eurofast</i> cordsets<br>and receptacles | <p>Male</p>   |
|         | <b>BS 8241-0/PG9</b> | PBT, Black<br>PG 7 cable gland,<br>accepts 4-8 mm cable diameter<br>85°C<br>125 V, 4 A |  |               |
|         | <b>B 8141-0/PG9</b>  | PBT, Black<br>PG 7 cable gland,<br>accepts 4-8 mm cable diameter<br>85°C<br>250 V, 4 A |  | <p>Female</p> |
|         | <b>B 8241-0/PG9</b>  | PBT, Black<br>PG 7 cable gland,<br>accepts 4-8 mm cable diameter<br>85°C<br>250 V, 4 A |  |               |