

### Identification ties and plates for marking cable bundles

#### • IT Ties





One of the major benefits is the ability to both secure and identify cable bundles at different times.

#### Features and Benefits

- Identification ties made of Polyamide 6.6
- For simple identification and securing of cable bundles in one step
- Can be marked either on-site or after bundling (Pen T82)
- In addition a large selection of labels are available





One operation with two benefits.



<b>MATERIAL</b>	Polyamide 6.6 (PA66)
<b>Operating Temperature</b>	-40 °C to +85 °C
<b>Flammability</b>	UL94 V2
<b>Specifications</b>	UL-Recognised

**HF** ✓ **RoHS** ✓



TYPE	Bundle Ø min.	Bundle Ø max.	Width (W)	Height (H)	Length (L)	Width (W2)	N	Recommended Labels	Pack Cont.	Colour	Article-No.
IT18FL	1.5	19.0	20.5	9.0	110.0	2.5	80	TAG18-07TD1	100	Natural (NA)	111-81919
IT18R	6.0	22.0	25.0	8.0	100.0	2.3	80	TAG23-06TD1	100	Natural (NA)	111-81821
IT50R	9.5	44.5	28.0	12.9	203.0	4.6	225	TAG23-10TD1	100	Natural (NA)	111-85019
IT50RD	10.0	44.0	29.0	26.3	205.0	4.7	225	TAG26-21TD1	50	Natural (NA)	111-85219
IT50RT	10.0	44.0	46.0	26.3	205.0	4.7	225	TAG43-21TD1	50	Natural (NA)	111-85119
IT50L	19.0	100.0	56.0	12.8	390.0	4.7	225	TAG52-10TD1	100	Natural (NA)	111-85319

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.

**N** = Minimum Tensile Strength

TYPE	Pack Cont.	Colour	Article-No.
T82S-BK	2	Black (BK)	500-50820
T82R-RD	2	Red (RD)	500-50822

Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.