



Anschlußmaße nach IEC 169-17
 dimensions according to IEC 169-17



Außenleiter / outer conductor	CuZn39Pb3	Cu2Ni5
Innenleiter / inner conductor	CuZn39Pb3	Cu1Ni2Au0.8
Crimprohr / crimp ferrule	Cu	Ni5
sonstige Metallteile / other metal parts	CuZn39Pb3	Cu2Ni5
Isolierung / insulator	PTFE	
Dichtung / gasket	Silicon	

Ⓐ Kabel / cable	G 5: RG-223/U; RG-400/U	Ⓑ
Montage / assembly	A0205	
VSWR (typisch / typical)	1.08 bei/at 1 GHz 1.12 bei/at 2 GHz 1.12 bei/at 3 GHz	Ⓑ
VSWR (nach IEC 169-17 / according to IEC 169-17)	?1.22 bis/up to 3 GHz	
Einfügedämpfung / insertion loss	?0.15 dB bis/up to 3 GHz	

b	7481	14.01.97	BE	88	Tag	Name	Werkstoff	
				Gez.	17.11.	RV		
				Gep.	26.11.96	BJ	Oberfläche	
				Norm				
a	7351	26.11.96	BJ	Maßstab	Benennung	TNC-Kabelstecker TNC-Straight Plug		
Maße ohne Toleranzang. nach	Unteri.-Art	K	Zeichn.-Nr.	J01010A2256				
Änd.-Zust.	Änderungs-Mitteilung	Tag	Name	Ersatz für				