

Bosch GBM 13 HRE Drill



Technical data: GBM 13 HRE Professional

Rated power input	550 W
No-load speed	0 – 550 rpm
Power output	285 W
Weight	2,1 kg
Rated speed	380 rpm
Rated torque	5,0 Nm
Max. torque	60,0 Nm
Drilling range	
Drilling dia. in aluminium	20 mm
Drilling dia. in wood	40 mm
Drilling dia. in steel	13 mm