

**ARCA 406021**



Sample photo

**Order symbol:** ARCA 406021  
**Product nbr:** 8120026  
**Description:** Cabinet, PC  
**Remarks:** 2-point locking

**EAN:** 6418074079374  
**EI. number:**  
 Finland: 3423124  
 Electric No. 8212091249  
 Denmark:  
 Electric No. Sweden: 2500117

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	400	600	210	MPP ARCA 4060	Mounting plate perforated (550x350x2 mm - 26x11 mm)
<b>inch:</b>	15.7	23.6	8.3	MPMP ARCA 6040	Mounting plate multiperforated (550x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 6040	Mounting plate (550x350 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 406021	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			IDS ARCA 4060	Inner door set
<b>Cover colour:</b>	RAL 7035 -light grey			PMK ARCA 60	Pole mounting kit
<b>Gasket material:</b>	Polyurethane			RCS ARCA 4060	Rain canopy set
Temperatures:				SBK ARCA 40	Support bar kit
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SBK ARCA 60	Support bar kit
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
<b>Temperature °F (short term):</b>	-40 ... 250 °F			DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				
Accessories:				<b>Rating:</b>	
MPS ARCA 6040	Mounting plate (550x350x2 mm)			Ingress Protection (EN 60529): IP66	
				Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 12 and 13	

**Certificates:**  
SGS Fimko

