

Main

| | |
|------------------------------------|--|
| Commercial Status | Commercialised |
| Range of product | OsiSense XS |
| Series name | Application |
| Sensor type | Inductive proximity sensor |
| Product specific application | Food and beverage |
| Sensor name | XS2 |
| Sensor design | Cylindrical M12 |
| Size | 61 mm |
| Body type | Fixed |
| Detector flush mounting acceptance | Non flush mountable |
| Material | Stainless steel |
| Type of output signal | Discrete |
| Wiring technique | 3-wire |
| [Sn] nominal sensing distance | 7 mm |
| Discrete output function | 1 NO |
| Output circuit type | DC |
| Discrete output type | PNP |
| Electrical connection | 4 pins M12 male connector |
| [Us] rated supply voltage | 12...24 V DC with reverse polarity protection |
| Switching capacity in mA | <= 200 mA with overload and short-circuit protection |
| IP degree of protection | IP69 K conforming to DIN 40050 IP67 conforming to IEC 60529 |

Complementary

| | |
|-----------------------|-------------------------------|
| ISO thread | M12 x 1 |
| Detection face | Frontal |
| Front material | PPS |
| Enclosure material | Stainless steel 316 L |
| Operating zone | 0...5.6 mm |
| Differential travel | 1...15% of Sr |
| Status LED | 1 LED yellow for output state |
| Supply voltage limits | 10...36 V DC |
| Switching frequency | <= 2500 Hz |
| Voltage drop | <= 2 V at closed state |
| Current consumption | <= 10 mA at no-load |
| Delay first up | <= 10 ms |
| Delay response | <= 0.2 ms |
| Delay recovery | <= 0.2 ms |
| Marking | CE |
| Threaded length | 37 mm |
| Length | 61 mm |
| Product weight | 0.035 kg |

Environment

| | |
|---------------------------------------|---|
| Product certifications | CSA UL |
| Ambient air temperature for operation | -25...85 °C |
| Ambient air temperature for storage | -40...85 °C |
| Vibration resistance | 25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn for 11 ms conforming to IEC 60068-2-27 |

RoHS compliance

| | |
|-----------------------------------|-----------|
| RoHS EUR status | Compliant |
| RoHS EUR conformity date(Y Y W W) | 0821 |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|