

FlexSQUARE / LED Permanent Beacon 853

LED Perm. Begcon BWM 48VAC CL



Part No.: 853.400.66

MECHANICAL DATA

Type of fixing

Service life optical

Product weight

Weight with packaging

Working temperature minimum

Working temperature maximum





| Length | 85 mm |
|------------------------------|-----------------------------|
| Width | 85 mm |
| Height | 72 mm |
| Materials | PC PP-GF |
| Dome colour | Clear |
| Housing colour | Black |
| Protection category | IP66 IP67 |
| Connection | Screw terminals |
| cross-sectional area maximum | 1,50mm ² / 16AWG |
| Cable entry | Membrane grommet |
| Cable entry minimum | d = 1 mm d = 6 mm |
| Cable entry maximum | d = 12 mm |

d = 9 mm

-25°C +50°C

163 g

136 g

Base mounting Wall mounting 50,000 h maximum

| ELECTRICAL DATA | |
|-----------------------------|--------------------|
| Operating voltage | 48V |
| Operating voltage type | AC |
| Operating voltage type | 50Hz |
| Operating voltage tolerance | +/- 10% |
| Rated operational voltage | 48 VAC |
| Rated operational current | 35 mA |
| Rated inrush current | 200 mA |
| Protection class | Protection class 2 |
| Pollution degree | 3 |


| OPTICAL DATA | |
|----------------------|-----------|
| Light source | LED |
| Light colour | White |
| Optical signal image | Permanent |

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



FlexSQUARE / LED Permanent Beacon 853

LED Perm. Beacon BWM 48VAC CL



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.