
NC A NA	112425.DWG	2425.DWG	C:/112/112425.DWG	DO NOT SCALE DRAWING	QIY	FINISH	MAIERIAL	DESCRIPTION	
RFV SIZE SCALE			CAD FILE		, ,				
112425			SHEET 1 OF 1	$1.180 - 4.724 = \pm 0.020$ "		NICKEL	BRASS	BODY	
· · · · · · · · · · · · · · · · · · ·	PART NO.				_ <b>_</b>	GOLD	PHOS. BRONZE	CONTACT PIN	2
				TOLERANCES FOR INCHES ARE:	_	NATURAL	DELRIN	INSULATOR	3
BNC BULKHEAD RECEPTACLE - 75 ohms	BNC BULKHEAD		ISSUED		_	NICKEL	BRASS	LOCK WASHER	4
				$30 - 30mm \pm 0.40mm$		NICKEL	BRASS	HEX NUT	σ
	PART DESCRIPTION		CHECKED	0.5 - 8mm ± 0.20mm		NICKEL	BRASS	SOLDER TAB	თ
		03/21/03	DRAWN G.R.S.	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:					7
				INCHES AND FOR CUSTOMER REFERANCE ONLY.					00
•	•	DATE	APPROVALS	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE					



## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol: <u>112425</u>