


Anschlußmaße nach IEC 169-17 / mating face according to IEC 169-17



Außenleiter / outer conductor	CuZn39Pb3	Cu2Ni5
Innenleiter / inner conductor	CuZn39Pb3	Cu1Ni2Au0.8
Crimprohr / crimp ferrule	Cu	Ni5
sonstige Metallteile / other metal parts	CuZn39Pb3	Cu2Ni5
Isolierung / insulator	PTFE	
Dichtung / gasket	Silicon	

Kabel / cable G 5: RG-223/U; RG-400/U
(a) RG-142B/U

Montage / assembly A0505

VSWR (typisch / typical) 1.09 bei/at 1 GHz
1.16 bei/at 2 GHz
1.24 bei/at 3 GHz

(a) VSWR (nach IEC 169-17 / according to IEC 169-17) ≤1.3 bis/up to 3 GHz

Einfügedämpfung / insertion loss ≤0.15 dB bis/up to 3 GHz

				92	Tag	Name	Werkstoff	
				Gez.	03.07.	Beyer		
				Gep.	03.07.92	RV		
				Norm			Oberfläche	
				Maßstab	Benennung			
				2:1	TNC-Kabelwinkelstecker TNC Angle Plug			
b a	9094 7456	12.05.98 08.01.97	KL BE	Maße ohne Toleranzang. nach	Unteri.-Art	Zeichn.-Nr.	J01010A0006	
					K			
Änd.-Zust.	Änderungs-Mitteilung	Tag	Name	Ersatz für				

