

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [90059-0007](#)
Status: **Active**
Overview: C-Grid III™
Description: 2.54mm Pitch C-Grid® Micro Shunt, Low Profile, 5.08µm Tin (Sn) Plating

Documents:

[3D Model](#) [Product Specification PS-90059 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Accessories
 Series [90059](#)
 Component Type Shunt
 Overview [C-Grid III™](#)
 Product Name C-Grid®, C-Grid III™, SL™
 UPC 800753722040

Physical

Circuits (Loaded) 2
 Color - Resin Black
 Flammability 94V-0
 Gender Female
 Lock to Mating Part None
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Polyester
 Net Weight 1.136/g
 Number of Rows 1
 Packaging Type Bag
 Plating min - Mating 5.080µm
 Plating min - Termination 5.080µm
 Temperature Range - Operating -55°C to +125°C
 Termination Interface: Style Surface Mount


Electrical

Current - Maximum per Contact 1.5A

Material Info

Reference - Drawing Numbers

Product Specification PS-90059, RPS-90059-002
 Sales Drawing SDA-90059



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[90059Series](#)

Use With

(0.64)/.025 square and round pins