


## Crocodile clips

### AGF 20



Product	AGF 20
description	Nickel-plated steel alligator clip. The special shape allows clamping of both extremely fine and thick wires. 4 mm diameter socket connection and solder connection possible. max. bolt diameter 12 mm
operating instruction	BA420
Articlenummer	930120000 <span style="float: right; border: 1px solid black; padding: 2px;">Ni</span>
<b>drawing</b>	
	
<b>technical data</b>	
connection	unsprung socket 4 mm, solder connection
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	4 A
material socket	steel, nickel plated
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +100 °C
clamping range	10 mm
standard	IEC 61010

4 mm system

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> without rated measurement category, for other circuits that are not directly connected to mains

stand: 19.06.2019