## MALLORY Mallory Sonalert Products Inc. Part # AST0927MW-03TRQ Sales Outline Drawing C


May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

	CID		TOT
NU	CIR	u	KY

NO CIRCUITAT				
Oscillation Frequency (Hz)	2731			
Operating Voltage (Vp-p)	2 ~ 5			
Rated Voltage (Vp-p)	3			
Current Consumption Max. (mA)	90 at Rated Voltage			
Sound Pressure Level (dB/min)	90 at 10cm at Rated Voltage			
Coil Resistance (Ω)	$16 \pm 3$			
Operating Temperature (°C)	-30 ~ +70			
Storage Temperature (°C)	-40 ~ +85			
Type of Connection Terminal	SMD			
Housing	LCP plastic resin (Color : Black)			
Weight (Grams)	0.8			
Condition by reflow soldering (°C)	$250 \pm 5$ / within 10 sec			
Condition by hand soldering (°C)	$350 \pm 20$ / within 5 sec			
Options	For other options contact factory			

**Dimensions:** (units: mm)

## **RoHS Compliant**



**Packaging:** Parts are supplied on tape and reel.

Units do not come with wash label and are not appropriate for aqueous wash.

