



1 2 3 4 5 6 7

A

A



- NOTES:**
- MATERIAL**
- 1.Insulator Material: PBT+30%GF(UL94V-0),Grey
 - 2.Contact Material : Brass
 - 3.Contact Plating :
 AWHW xxG-0202-T: Gold flash/Tin Over Ni
 AWHW xxG-0102-T: 30u"Au/Tin Over Ni
- ELECTRICAL**
- 1.Current Rating: 3AMP\
 - 2.Voltage Rating: 250V
 - 3.Withstand Voltage: 500V AC/Minute
 - 4.Contact Resistance : 20mΩ max
 - 5.Insulation Resistance: 1000MΩ min
- ENVIRONMENTAL**
- 1.Operation Temperature: -40°C to +105°C
 - 2.Packing: Tray packing

B



B

C

C

D

D



Order information:
 xx : 06,08,10,12,14,16,18,20,24
 26,30,34,40,50,60,64

Dimension antitheses list	
NO. Pin	L
6P-8P	4.00
10P-64P	4.40

E

E

F

F

RoHS compliant
 Unit: mm



Scale	Free	⑥	Cancel solder profile	12.10.2020	Daniel		Date	Name	Customer-No.
TOLERANCE		⑤	Add voltage rating	09.07.2019	Xavier	Drawn	25.01.2006	Alex	
X.X	±0.40	④	Add UL file no.	12.12.2013	Amy	Approved	12.10.2020	Daniel	ASSMANN WSW-No.
X.XX	±0.25	③	Add the plating Au 30u"	23.10.2013	Winnie				AWHW xxG-0202-T AWHW xxG-0102-T
X.XXX	±0.15	②	Update	29.06.2009	Dean				Drawing-No.
DIM	TOL	①	Drawn	25.01.2006	Alex				ASS 2314 CO
Angle	± 3°	Id.	Modification	Date	Name				rev06
									Replace

H

H

1 2 3 4 5 6 7