

# Push Button Switch

**Q-10226**

TYPE: **R13-527BL**

## SPECIFICATIONS

Rating: 10A 12V DC  
Contact R: 50mΩ max  
Insulation R: 500V DC 100MΩ min  
Dielectric Strength: 1 Minute 1000V AC  
Operating Temperature: -25°C ~ +85°C  
Electrical Life: 10, 000 Cycles

Outline Drawing

