

AR - ISORYL screwdrivers for slotted-head screws - milled blade





Standards:

NF ISO 2380-1, NF ISO 2380-2,
ISO 2380-1, ISO 2380-2, DIN ISO
2380-1, DIN ISO 2380-2, ASME
B107.600

Description:

- Round blade milled for access to the bottom of the well.
- Finish: polished chromed.



	Diameter [mm]	Length L [mm]	Length L2 [mm]	Thickness E [mm]	Weight [g]	Length L1 [mm]	Diameter D1 [mm]
AR.2.5X50	16.0	120.0	70.0	0.4	15.0	50.0	2.5
AR.2.5X75	16.0	145.0	70.0	0.4	16.0	75.0	2.5
AR.2X40	16.0	110.0	70.0	0.4	13.0	40.0	2.0
AR.3.5X100	20.5	180.0	80.0	0.8	33.0	100.0	3.5
AR.3.5X75	20.5	155.0	80.0	0.6	31.0	75.0	3.5
AR.3X75	16.0	145.0	70.0	0.5	17.0	75.0	3.0
AR.4X100	24.0	190.0	90.0	0.8	45.0	100.0	4.0
AR.4X150	24.0	240.0	90.0	0.8	50.0	150.0	4.0
AR.5.5X100	28.0	200.0	100.0	1.0	71.0	100.0	5.5
AR.5.5X150	28.0	250.0	100.0	1.0	80.0	150.0	5.5
AR.5.5X200	28.0	250.0	100.0	1.0	80.0	150.0	5.5
AR.6.5X100	30.0	210.0	110.0	1.2	102.0	100.0	6.5
AR.6.5X150	30.0	260.0	110.0	1.2	114.0	150.0	6.5
AR.6.5X200	30.0	310.0	110.0	1.2	226.0	200.0	6.5
AR.8X150	30.0	260.0	110.0	1.2	141.0	150.0	8.0