


## 7/8" FEMALE FLANGE PLUG


Wire 5X0.75 0.5m

Flange 7/8" female  
with multi-strand wire  
5-pole


### [Link to Product](#)

#### Illustration



*stay connected*

Female



Product may differ from Image

**Form**

78381

**Technical Data**

Operating voltage	max. 230/400 V AC/DC
Operating current per contact	max. 9 A
Locking of ports	Screw thread 7/8" (recommended torque 1.5 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)
Connection	pre-wired with PVC-wire isolation, (UL/CSA)

**Cables**

Cable number	978
No./diameter of wires	5 × AWG18
Wire isolation	PVC (br, wh, bl, bk, gnye)
Shore hardness outer jacket	75 ± 5A
Material (wire)	UL-Listed
Bend radius (fixed)	10 × outer diameter

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 11/14

Bend radius (moving)	15 × outer diameter
Temperature range (fixed)	-25...+85 °C
Temperature range (mobile)	-10...+50 °C

**General data**

Temperature range	-25...+85 °C
-------------------	--------------

**Commercial data**

country of origin	DE
customs tariff number	85444290
minimum order quantity	1