



DIM. A = 2.50 X No. of Spaces
 DIM. B = DIM. A + 5.00
 DIM. C = DIM. A + 3.60

* Available in 2 through 15 Circuits

Material:

- * Material: Nylon 46 UL 94V-0
Color Ivory
- * Contact: Brass, round pins

Ordering Code:

CI25 ** P 1 H 00 -LF
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② No. of Circuits
- ③ Contact type: P= Pin header
- ④ Plating option:
1 = $3.05 \mu\text{m}$ (120μ) Matte Tin
over $0.76 \mu\text{m}$ (30μ) Nickel
- ⑤ Tail Style: H= Right Angle
- ⑥ Option: 00= UL 94V-0(Standard)
- ⑦ LF= For Lead Free IR Processes

Recommended P.C. Board Layout

RoHS Compliant

| | | | | | | | | | | |
|-----|------|------|--------------------|--|-----------|---|-----------------|---|------------------------------------|-------------------------|
| 4 | | | | | | DATE | UNIT: mm / inch | TITLE: 2.50MM(.098") RIGHT ANGLE HEADERS | 瀚荃股份有限公司 CviLux Corporation | |
| 3 | | | DRAWN BY: Jim | | 08/17-06' | TOLERANCE UNLESS OTHERWISE SPECIFIED | | MATERIAL: | | |
| 2 | | | ENGINEER: Eisley | | 08/24-06' | .X ± 0.30/.012 X.* ± 1' | | | | |
| 1 | | | CHECKED BY: David | | 08/24-06' | .XX ± 0.20/.010 .X.* ± | | FINISH: | | |
| SYM | NAME | DATE | APPROVED BY: David | | 08/24-06' | .XXX ± 0.10/0.04 .XX.* ± | | | DRAWING NO. CI2517SA | PART NO. CI25**P1H00-LF |
| | | | | | | | | | SCALE 3 / 1 | SHEET 1 OF 1 |