



SECTION A-A




SECTION B-B



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Phosphoric brass Tin-plated
- 8、Applicable Wire Sizes:AWG #28~32#

			GENERAL TOLERANCE		制 图 DRAWING		 <b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO., LTD					
			DIM	TOL	审 核 CHECK							
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	1.0 端子	版本 REV.	A		
1			初版发行		X. XX		±0.20	产品料号 PART NO.	HC-1.0-T	单 位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X. XXX		±0.10		比 例 SCALE			材 料 MATERIAL	页 次 SHEET	1/1
			Angle		±3.0°		投 影 Projection	