



Sym	Attachment Type
D	Bead Chain, Cres., Passivate
F	Wire Rope, Nylon Jacket
G	Nylon Rope
H	Wire Rope, Teflon Jacket
R	Wire Rope, PVC Jacket
S	#8 Sash Chain, Cres., Passivate
T	Wire Rope, No Jacket
U	Wire Rope, Polyurethane Jacket with Terminal




Dash No.	K DIA
01	.140 (3.6)
02	.182 (4.6)
03	.191 (4.9)
04	.197 (5.0)
05	.167 (4.2)
06	.125 (3.2)
07	.218 (5.5)
09	.156 (4.0)
00	No Eyelet


SPLIT RING - Style C



SOLID RING - Style B



SOLID RING - Style A



Dash No.	L Dia. ±.015 (0.4)	Dash No.	L Dia. ±.015 (0.4)
50	.425 (10.8)	74	1.625 (41.3)
52	.485 (12.3)	76	1.750 (44.5)
54	.640 (16.3)	78	1.875 (47.6)
56	.750 (19.1)	80	1.980 (50.3)
58	.890 (22.6)	82	2.060 (52.3)
60	1.015 (25.8)	84	2.235 (56.8)
62	1.095 (27.8)	86	2.310 (58.7)
64	1.130 (28.7)	88	2.475 (62.9)
66	1.250 (31.8)	90	2.655 (67.4)
68	1.350 (34.3)	92	2.810 (71.4)
70	1.390 (35.3)	94	3.045 (77.3)
72	1.485 (37.7)		

Dash No.	M Dia. ±.015 (0.4)	Dash No.	M Dia. ±.015 (0.4)
08	.468 (11.9)	24	1.484 (37.7)
10	.593 (15.1)	25	1.577 (40.1)
11	.265 (6.73)	27	1.640 (41.7)
12	.718 (18.2)	28	1.687 (42.8)
13	.765 (19.4)	29	1.765 (44.8)
14	.844 (21.4)	30	1.890 (48.0)
15	.890 (22.6)	31	1.953 (49.6)
16	.968 (24.6)	32	1.968 (50.0)
17	1.015 (25.8)	33	2.077 (52.8)
18	1.093 (27.8)	35	2.140 (54.4)
19	1.140 (29.0)	36	2.187 (55.5)
20	1.203 (30.6)	40	2.406 (61.1)
21	1.265 (32.1)	44	2.656 (67.5)
22	1.343 (34.1)	48	3.031 (77.0)
23	1.453 (36.9)		

Dash No.	N Dia. ±.015 (0.4)	Dash No.	N Dia. ±.015 (0.4)
095	.312 (7.9)	109	1.266 (32.2)
100	.391 (9.9)	209	1.312 (33.3)
101	.516 (13.1)	110	1.391 (35.3)
102	.583 (14.8)	210	1.438 (36.5)
103	.641 (16.3)	111	1.521 (38.6)
104	.708 (18.0)	211	1.536 (39.0)
105	.766 (19.5)	112	1.641 (41.7)
205	.788 (20.0)	113	1.766 (44.9)
106	.896 (22.2)	213	1.812 (46.0)
206	.907 (23.0)	114	1.891 (48.0)
107	1.016 (25.8)	214	1.938 (49.2)
207	1.025 (26.0)	115	2.078 (52.8)
108	1.141 (29.0)	116	2.406 (61.1)
308	1.188 (30.2)	117	2.510 (63.8)
208	1.203 (30.6)		

Metric dimensions (mm) are indicated in parentheses.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[670-001F01-01-3](#) [670-001S01-01-6](#) [670-001D01-01-2.5](#) [670-001D02-02-4](#) [670-001G01-01-6](#) [670-001S03-01-6](#)
[670-001G06-00-14](#) [670-001D01-01-6](#) [670-001D01-101-2](#) [670-001D01-104-4.25](#) [670-001D01-104-4.5](#) [670-001D01-206-4](#) [670-001D05-50-4](#) [670-001F01-01-10](#) [670-001F01-01-5](#) [670-001F01-01-6](#) [670-001F01-01-7](#) [670-001F01-01-8](#)
[670-001F01-07-5](#) [670-001F01-102-2.25](#) [670-001F01-112-5-53](#) [670-001F01-16-6](#) [670-001F01-18-6](#) [670-001F01-20-4](#) [670-001F01-30-6](#) [670-001F01-58-6](#) [670-001F02-01-5](#) [670-001F02-02-5](#) [670-001F02-02-7](#) [670-001F02-02-8](#) [670-001F03-03-7](#) [670-001F04-04-13.5](#) [670-001F04-04-17](#) [670-001F04-04-18.50](#) [670-001F06-06-1.75](#) [670-001F06-06-3](#) [670-001F06-107-4](#) [670-001F06-18-6](#) [670-001F06-50-4.25](#) [670-001F07-00-8](#) [670-001F07-09-3](#) [670-001F09-09-3](#) [670-001G00-06-3](#) [670-001G01-01-1.44](#) [670-001G01-01-2.0](#) [670-001G01-01-3](#) [670-001G01-01-3.50](#) [670-001G01-102-4](#) [670-001G01-60-4](#) [670-001G04-08-4](#) [670-001G05-00-10.5](#) [670-001G06-00-5](#) [670-001G06-06-2.25](#) [670-001G07-01-5](#) [670-001G105-105-6-181](#) [670-001G108-108-6-181](#) [670-001H01-01-1](#) [670-001H01-01-12-181](#) [670-001H01-01-3](#) [670-001H01-01-4](#) [670-001H01-01-4.5](#) [670-001H01-01-5](#) [670-001H01-02-2.5](#) [670-001H01-06-4](#) [670-001H01-08-8](#) [670-001H01-10-08](#) [670-001H01-12-14C](#) [670-001H01-12-4](#) [670-001H01-12-8](#) [670-001H01-50-18](#) [670-001H01-52-12](#) [670-001H01-54-4](#) [670-001H01-54-8](#) [670-001H02-02-6](#) [670-001H03-10-6.75](#) [670-001H04-04-12](#) [670-001H04-08-3.25](#) [670-001H04-12-2](#) [670-001H04-13-2](#) [670-001H04-56-2](#) [670-001H05-05-5](#) [670-001H06-06-2](#) [670-001H06-06-2.5](#) [670-001H06-06-3](#) [670-001H06-09-4](#) [670-001H07-09-17.5](#) [670-001H09-09-2.5](#) [670-001R01-01-2.5](#) [670-001R01-01-4.5](#) [670-001R01-01-7.5](#) [670-001R03-18-6](#) [670-001R04-106-2](#) [670-001R05-01-6](#) [670-001R05-05-4](#) [670-001R05-05-5](#) [670-001R06-06-1.25](#) [670-001S01-01-2.5](#) [670-001S01-01-4](#) [670-001S01-01-4.5](#) [670-001S01-01-5](#)