


Art.-No.	VE	PG	EAN
227120011	1	131	 4 008224 565837

POWERversal 10-way, 250V~, 16A, max.3600w, IP20, with shutter, with 90° turned sockets, 65mm distance between sockets, mountable, reconnectable, cable 05VV-F3Gx1,5mm², 1,4m, length (lxbxh):(872,6x71x58,3)mm, silver-black



Technical data		227120011
Housing shape	Rectangular	
Material	Plastic	
Material quality	Thermoplastic	
Surface finishing	Matt	
Colour	Silver	
Colour (user defined)	silver/black	
Degree of protection (IP)	IP20	
Angle rotated central insert	90°	
Number of socket outlets with protective contact	10	
Residual current circuit breaker (RCCB)	No	
Mains filter	No	
Over voltage protection	No	
Nominal current	16A	
Core cross section	1.5mm ²	
With cover	No	
Transparent	No	
Length of power cord	1.4m	
Rotated central insert	Yes	