



Nr no	Artikel-Nr. part no.	LP-Dicke pcb-thickness	Kontaktlänge contact length	a ± 0,1
1	09 03 000 9950	3,0 ± 0,4	20,0 ± 0,3	11,75
2	09 03 000 9951	4,0 ± 0,4	20,0 ± 0,3	10,7
3	09 03 000 9952	1,6 ± 0,4	17,0 ± 0,3	9,9
		4,8 ± 0,4	20,0 ± 0,3	
4	09 03 000 9953	2,4 ± 0,4	17,0 ± 0,3	9,1
		5,6 ± 0,4	20,0 ± 0,3	
5	09 03 000 9954	3,2 ± 0,4	17,0 ± 0,3	8,3
		6,4 ± 0,4	20,0 ± 0,3	
6	09 03 000 9955	4,0 ± 0,4	17,0 ± 0,3	7,5
		7,2 ± 0,4	20,0 ± 0,3	
7	09 03 000 9956	1,6 ± 0,4	13,2 ± 0,3	6,7
		4,8 ± 0,4	17,0 ± 0,3	
8	09 03 000 9957	2,4 ± 0,4	13,2 ± 0,3	5,9
		5,6 ± 0,4	17,0 ± 0,3	
9	09 03 000 9958	3,2 ± 0,4	13,2 ± 0,3	5,1
		6,4 ± 0,4	17,0 ± 0,3	
10	09 03 000 9959	4,0 ± 0,4	13,2 ± 0,3	4,3

All Dimensions in mm Original Size DIN A 3	Techn. Character.			Nicht tolerierte Maß / Free size tolerances	
		Dat.	Name	Maßstab / Scale	
				1:1	
				2:1	
				DIN Signal Bauform C/R Übergaberahmen Einpress DIN signal type C/R shroud press-in	
32597	HARTING Electronics GmbH & Co. KG				TB 09 03 000 995x
Mod.	Dat.	Name	D-32339 ESPELKAMP		
				Sub.	Blatt / page