


mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCJ		www.fciconnect.com	
ltr	ecn no	dr	date	.X ± 0.30	projection	title			
H	T06-0074	AC	4/10/06	.XX ± 0.20	MM	MINI USB B-TYPE SMT RECEPTACLE			
J	T06-0137	AC	7/18/06	.XXX ± 0.10	scale	product family 511			
K	T06-0201	AC	12/14/06	0° ±2°	N/A	size A4			
L	T07-1002	JH	1/5/07	JASON HSU 12/27/10		code TWN			
M	T10-0095	JH	12/27/10	JASON HSU 12/27/10		sheet 1 of 2			
N	T-004667	JH	7/27/11	GARY HSIEH 12/27/10		10033526			
sheet index	revision sheet	N 1	N 2	JOSEPH HSIA 12/27/10					




PROD. NO
SEE NOTES

5. PRODUCT ORDERING DATA :
FOR LEAD-FREE




- NOTES:
1. MATERIAL:
HOUSING: THERMOPLASTIC. UL 94V-0 RATED, COLOR: BLACK.
CONTACT: COPPER ALLOY.
SHELL: COPPER ALLOY
MYLAR: KAPTON TAPE.
2. FINISH:
CONTACT: UNDERPLATED 50u" MIN. NICKEL OVERALL
100u" MIN. MATTE TIN PLATED ON SOLDERING AREA,
SELECTIVE GOLD PLATED ON CONTACT AREA.
SHIELD: CODE N: NICKEL 40u" ~120u" PLATED OVERALL.
T: SELECTIVE 60u" MIN. MATTE TIN ON LEGS OVER 40u" ~120u" NICKEL.
 3. 10033526-X3212XLF MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBE
IN GS-22-008 AND ITS HSG WILL WITHSTAND EXPOSE TO 260 DEGREE C
PEAK TEMPERATURE FOR 10 SECONDS IN A IR REFLOW APPLICATION.
 4. PRODUCT SPEC: GS-12-174 ; PACKAGE SPEC: GS-14-873.



CONNECTOR PROFILE

RECOMMENDED PCB LAYOUT FOR 10033526-XXXIXX
GENERAL TOLERANCE +/- 0.05mm



mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		www.fciconnect.com	
itr	ecn no	dr	date	linear	projection	title	
N				.X ± 0.30	MM	MINI USB B-TYPE SMT RECEPTACLE	
				.XX ± 0.20	MM	product family	511
				.XXX ± 0.10	MM	size	dwg no
				0° ± 2°	MM	scale	A4
				dr	JASON HSU 12/27/10	sheet	2 of 2
				engr	JASON HSU 12/27/10	code	TWN
				chr	GARY HSIEH 12/27/10	product family	511
				appd	JOSEPH HSIA 12/27/10	size	dwg no
sheet	revision					code	10033526
index	sheet					sheet	2 of 2

