

PRODUCT NUMBER  
57202-XXX-XXXXLFL

ROHS COMPATIBLE  
SEE NOTE 7

POLARIZATION, SEE NOTE 6

PACKAGING, SEE NOTE 5

NB OF POS PER ROW : 02 TO 25







PLATING  
S = 0.38µm GOLD/GXT ON CONTACT AREA  
2µm MIN MATTE TIN ON TAIL  
G = 0.76µm GOLD/GXT ON CONTACT AREA  
2µm MIN MATTE TIN ON TAIL  
F = GOLD FLASH ON CONTACT AREA  
2µm MIN MATTE TIN ON TAIL  
T = 2-6.0µm FULL MATTE TIN  
1.27µm MIN NICKEL UNDERPLATING

STYLE	POST LENGTH ±0.2
51	2.00
52	4.00
53	3.50
54	2.50

NOTES:

- MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC  
UL 94V-0, COLOR BLACK
- MATERIAL TERMINAL: COPPER ALLOY
- TO DETERMINE DIMENSIONS:  
N = NUMBER OF POSITIONS PER ROW.
- 7N MIN. PIN RETENTION IN EITHER DIRECTION.
- PACKAGING:  
= STANDARD PACKAGING IN POLYBAGS  
- POLYBAGS PACKAGING WHEN POLARISATION FEATURE APPLICABLE.  
U = TUBE AVAILABLE FROM 04 TO 25 POS PER ROW.  
A = TAPE AND REEL WITH PICK UP CAP, AS AVAILABLE  
K = TAPE AND REEL WITHOUT CAP, AS AVAILABLE.
- FOR POLARIZATION, SPECIFY POSITION NUMBER TO OMIT PIN.  
EXAMPLE : 03 = OMIT PIN POSITION 3, SEE TOP VIEW.  
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- ROHS COMPATIBLE PRODUCT SPECIFICATIONS

- d - PLATING:  
- "LF" MEANS THE PRODUCT IS LEAD-FREE,  
2µm MINIMUM MATTE TIN OVER 1.27µm  
MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY  
- THE HOUSING WILL WITHSTAND EXPOSURE TO  
260°C PEAK TEMPERATURE FOR 30 SECONDS  
IN A CONNECTION, INFRA-RED OR VAPOR  
PHASE REFLOW OVEN.
- c - LABELLING:  
- MEETS PACKAGING SPECS AS PER GS-14-920  
- LEGAL STATEMENT : SEE GS-47-0004



mat'l. code	ISO 1302	surface	tolerance	ISO 406	ISO	projection
ltr	ecn no	dr	date	tolerances unless otherwise specified	XX	mm
L	109-0087	J00	09.09.04		XX	±0.3
M	F11-0028	LWU	11.05.12		XXX	±0.13
N	B-19190	LWU	14.10.24		XXX	±0.05
P	B-19797	AMA	14.12.16	dr	LMULIN	04.05.06
R	B-19988	LWU	15.01.13	eng	JLCOMPAGNON	04.11.25
S	B-20032	AMA	15.01.20	chr	JM.C	04.11.25
T	F-23051	AMA	16.01.15	appd		

product family	MINITEK
title	UNSH HEADER
dwg no	2.00 mm VERTICAL SMT
sheet 1 of 1	size A3
type	CUSTOMER Drawing
sheet	revision
index	sheet