



YSV14H

by Burndy
Catalog ID: YSV14H

UNINSULATED BUTT SPLICE, 600 VOLTS MAXIMUM.

Product Details

General

Connector Type	Splice
Die Index	36
Feature - Barrel Style	Shrouded
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	90
Trade Name	HYLINK™
Type	Splice
UPC	781810805718
UPC 12 Digit	7818108057188

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.24 in
Dimension - Inside Diameter inch	0.09 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Strip Length inch	1/4

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	12
Conductor - Copper Solid Size Range	12
Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Navy Size	2 1/2 (1);2 1/2 (19);2 1/2 (26);3 (7);4 (1);4 (7);4 (19);4 (41)
Conductor - Copper Str Navy Size Range	2 1/2 (1)-4 (41)

Conductor - Copper Str Size	20;18;16;14
Conductor - Copper Str Size Range	20-14
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)