



RECOMMENDED
PC MOUNTING

MATERIALS:

- Body: Tarnish Resistant Nickel Plated Brass
- Body Mounting Pins: Nickel Plated Brass
- Center Contact: Gold Plated Beryllium Copper
- Center Mounting Pin: Gold Plated Brass
- Dielectric: Teflon per ASTM-D-1457

RATINGS:

- Operating Voltage: Hands free usage in controlled voltage environments: 500 Vrms maximum. *For CE compliance:* not intended for hand-held use at voltages above 33 Vrms/70 Vdc.
- Operating Temperature: -85°F to +329° F (-65°C to +165°C).
- Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4578

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4578](#)