










Number of contacts

3+

10 A 230/400 V 4 kV 3
10 A 250 V 4 kV 3

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han A®, Han-Quick Lock® termination, Contact surface: Silver plated  Blue slide	0,5 ... 2,5	09 20 003 2633	09 20 003 2733	 
Han A®, Han-Quick Lock® termination, Contact surface: Silver plated  Black slide	0,25 ... 1,5	09 20 003 2634	09 20 003 2734	
Han A®, Screw termination, Contact surface: Silver plated 	0,75 ... 1,5	09 20 003 2611	09 20 003 2711	    <p>Contact arrangement (view from termination side) Stripping length 4.5 mm Tightening torque 0.25 Nm</p>