Home ▸ plugs ▸ plugs ▸ BSB 20 K

main menue

home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
- 2 mm system
- 2 mm safety system
- 4 mm system
- 4 mm sliding sleeve system
- 4 mm safety system

sockets
sets
miscellaneous

company


portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

# BSB 20 K

**datasheet for BSB 20 K**
**article number: 930729100**



View Full-Size Image

| product description: | order number: 930 729-100 |
|---|---|
| **description:** | Multiple-spring wire plug with cable gland and 4 mm socket for onward connection cabability. Screw connection up to maximum cable cross-section of 2.5 mm² and external diameter of 4 mm. Nickel-plated brass contact material. |
| **typ:** | BSB 20 K schwarz/black |
| **system:** | 4mm system |
| **order number:** | 930 729-100 |
| **color** | ● |
| **other color versions:** | ● ● ● ● ● |
| **technical data** | |
| **measurement category acc. to IEC 61010:** | CAT I |
| **pin dimensions** | 4 mm |
| **type of contact:** | pin (spring loaded) |
| **type of termination:** | screw |
| **rated voltage:** | 30 VAC / 60 VDC |
| **rated current:** Please consider derating curve! | 30 A |
| **contact resistance:** | 10 mOhm |
| **material** | |
| **contact material:** | brass |
| **contact surface material:** | nickel |
| **housing material:** | PP |
| **environmental conditions:** | |
| **temperature range:** | -25 °C to +100 °C |
| **inflammable class:** | |
| **housing (basic material):** | UL 94 HB |
| **drawing** | |
| |  |



search online catalogue

Search

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code

© 2015 www.sks-kontakt.de
is Free Software released under the GNU General Public License.