

spiral plastic tubing PUN-8X1,25-S-6-BL

Part number: 197595

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	6 m
Outside diameter	8 mm
Block length	0.904 m
Inside diameter	5.7 mm
Coil diameter	60 mm
Number of windings	87
Temperature dependent operating pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-35 ... 60 °C
Authorisation	TÜV
Product weight	440 g
Pneumatic connection	For push-in connector outside diameter 8 mm for barbed connector internal diameter 6 mm with nut for barbed connector internal diameter 6 mm
Colour	blue
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE
Material tubing	TPE-U(PU)