



IB-129SSK-B
Mobile Rack for
3.5"/2.5" SATA/SAS HDD

Key features

- Mobile Rack with HDD Carrier
- Supports all 3.5"/2.5" SATA/SAS 1.5/3.0/6.0 Gbit/s HDDs (1" high) in a 5.25" bay
- Fits in a standard 5.25" bay
- Special aluminium case for better heat evacuation
- Supports Hot Swap
- Key lock to prevent improper operation
- Fanless design, no noise
- 12V power connector for additional fan by need

Cooling aluminium

This mobile rack has an efficient passiv cooling system. The design of the aluminium case can dissapate enough heat to guarantee silent and stable operations without installing a fan.



Technical data

Model	IB-129SSK-B	Hot Swap	Yes
Article No.	20048	Plug & Play	Yes
EAN code	4250078188438	Host connection	1x SATA power connector 15Pin, 1x SATA data connector 7Pin
Brand	ICY BOX	Transfer rate	Up to 6 Gbit/s
Article text	Mobile Rack for 3.5"/2.5" SATA/SAS HDD	Operating system	OS independent
Colour	Black	LED	Power and HDD access
Material	Aluminium	Alarm	No
HDD size	3.5"	Lock	Yes
HDD interface	1x SATA 1.5/3.0/6.0 Gbit/s	Power switch	No
HDD height	Up to 25.4 mm (1")	Fan	Fanless
HDD capacity	Unlimited	Power connection	1x 15pin SATA power
Required space	1x 5.25"		




Front view



Lock

LED shows power and HDD access



Fan power connector

On/Off switch for LED

SATA power connector 15Pin
SATA data connector 7Pin

Rear view

Packing content: 1x IB-129SSK-B, 2x keys, 8x screws

Logistical data

Packing unit:	20 pcs./carton	Dimension / carton:	420x330x262 mm
Total weight:	11.26 kg/carton	Dimension (incl. packing):	46x197x154 mm
Gross weight (inc. packing):	0.525 kg	Dimension from article:	186x146x41 mm
Net weight:	0.422 kg	Country of origin:	China