



main menu



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - ▶ 2 mm system
 - ▶ 2 mm safety system
 - ▶ 4 mm system
 - ▶ 4 mm safety system
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ sockets ▶ 4 mm safety system ▶ sockets ▶ 4 mm safety system ▶ BUELA 300 K

BUELA 300 K

datasheet for BUELA 300 K
article number: 931667100



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 931 667-100
description:	Multiple-spring wire plug, shatter-proof, flexible insulated sleeve with transverse hole. Lateral supports provide protection against contact when plugged in at right angles. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm ² .
typ:	BUELA 300 K schwarz/black
system:	4mm system
order number:	931 667-100
color:	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions:	4 mm
type of contact:	pin (spring loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	30 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	