



main menu



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
  - ▶ 2 mm system
  - ▶ 2 mm safety system
  - ▶ 4 mm system
  - ▶ 4 mm sliding sleeve system
  - ▶ 4 mm safety system
- sockets
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ plugs ▶ plugs ▶ BUELA 30 K

## BUELA 30 K

datasheet for BUELA 30 K  
article number: 930727104



[View Full-Size Image](#)



search online catalogue

Search

 

Messetermine

SPS/IPC/DRIVES  
24. 11. 2015 - 26. 11. 2015

QR-Code



<b>product description:</b>	order number: 930 727-104
<b>description:</b>	Multiple-spring wire plug, shatter-proof, flexible insulated sleeve with transverse hole. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm <sup>2</sup> . Nickel-plated brass contact material.
<b>typ:</b>	BUELA 30 K gruen/green
<b>system:</b>	4mm system
<b>order number:</b>	930 727-104
<b>color:</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>pin dimensions:</b>	4 mm
<b>type of contact:</b>	pin (spring loaded)
<b>type of termination:</b>	solder
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>rated current:</b>	30 A
<b>Please consider derating curve!</b>	
<b>contact resistance:</b>	3 mOhm
<b>material</b>	
<b>contact material:</b>	brass
<b>contact surface material:</b>	nickel
<b>housing material:</b>	PVC - P
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +70 °C
<b>drawing</b>	