

Monday, 03 December 2012



www.sks-kontakt.de

News contact sitemap Login

main menu

- home
- products
- skills
- download

Home > plugs > plugs > BUELA 30 K

BUELA 30 K

datasheet for BUELA 30 K
article number: 930727103



View Full-Size Image

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
 - > 2 mm system
 - > 2 mm safety system
 - > 4 mm system
 - > 4 mm sliding sleeve system
 - > 4 mm safety system
- sockets
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

search online catalogue



Search

Messetermine

No events

Newsletter Anmeldung

Test & Measurement

QR-Code



product description:	order number: 930 727-103
description:	Multiple-spring wire plug, shatter-proof, flexible insulated sleeve with transverse hole. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm ² . Nickel-plated brass contact material.
typ:	BUELA 30 K gelb/yellow
system:	4mm system
order number:	930 727-103
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	30 A
<i>Please consider derating curve!</i>	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	

© 2012 www.sks-kontakt.de

Joomla! is Free Software released under the GNU General Public License.