



HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45
35410 Hungen
Germany

phone: +49 (0) 6402/808-0
fax: +49 (0) 6402/808-60
email: info@hahn-trafo.de

Data sheet: BV 201 0148

Size 1 a: height 15 mm

Type BV 201...


0,35 VA

shipping unit per box: **50 pcs.** / temperature class: **ta 70/B** / weight: **approx. 25g**

- absolutely short circuit proof
- **excellent function at thermal changes, vacuum casted**
- maximum safety and long-term durability
- **with VDE-, ENEC 10-, UL-, and CSA certificates**
- minimum size, maximum capacity
- **self-extinguishing cast housing and sealing material**
- individually tested with certificate

Article no. BV	Output ta 70°C/B	prim.V	Connecting pins	Operating point sec. ± 5%	Connecting pins	No-load voltage V ± 5%
BV 201 0148	0,35	230	1-4	2 x 15 V 12 mA	5-6/7-8	2 x 25

Certificates



Dimensions with no indication of tolerances: ± 0,3 mm