



# HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45  
35410 Hungen  
Germany

phone: +49 (0) 6402/808-0  
fax: +49 (0) 6402/808-60  
email: info@hahn-trafo.de

## Data sheet: BV EI 305 2879

Size 5 a: height 29.8 mm

2,3 VA

ta 70/F

BV EI 305 ...

Several hundreds of typen provide high electrical safety and long service-life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open-circuit (no-load) loss capacity are also available in the range.

absolutely short-circuit-proof

**minimal size**

test certifications to ENEC 10-, VDE, UL- and CSA-regulations

**vaccum encapsulated, bobbin with dual chamber windings**

temperature class ta 40°C/F and ta 70°C/F

**high electrical safety and long service-life properties**


individually tested with certificate

**excellent temperature fluctuation resistance properties**


self-extinguishing cast housing and sealing material




Article no. BV	Output ta 40°C/F	prim.V	Connecting pins	Operating point sec. ± 5%	Connecting pins	No-load voltage V ± 5%
BV EI 305 2879	2,3	230	1-5	9 V 255 mA	7-9	17,6



Ansicht auf die Stifte



Lötstift 0,6x0,8/  
Rundpin  $\varnothing$ 0,8



Maße ohne Toleranzangabe  $\pm$  0,3 mm,  
Ausführungsänderungen vorbehalten

Dimensions with no indication of tolerances  $\pm$  0,3mm.