



# HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45  
35410 Hungen  
Germany

phone: +49 (0) 6402/808-0  
fax: +49 (0) 6402/808-60  
email: info@hahn-trafo.de

## Data sheet: BV EI 306 2077

Size 6 a: height 33.8 mm

3,2 VA

ta 40/F

BV EI 306 ...

Several hundreds of typen provide high electrical safety and long service-life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open-circuit (no-load) loss capacity are also available in the range.

absolutely short-circuit-proof

**minimal size**

test certifications to ENEC 10-, VDE, UL- and CSA-regulations

**vaccum encapsulated, bobbin with dual chamber windings**

temperature class ta 40°C/F and ta 70°C/F

**high electrical safety and long service-life properties**


individually tested with certificate

**excellent temperature fluctuation resistance properties**



self-extinguishing cast housing and sealing material



Article no. BV	Output ta 40°C/F	prim.V	Connecting pins	Operating point sec. ± 5%	Connecting pins	No-load voltage V ± 5%
BV EI 306 2077	3,2	230	1-5	2x12 V 133 mA	6-7/9-10	22,6/22,6



Ansicht auf die Stifte



Maße ohne Toleranzangabe ± 0,3 mm,  
Ausführungsänderungen vorbehalten

Dimensions with no indication of tolerances ± 0,3mm.