



Rectangular Horn Speakers – EH15V / EH30V



Rectangular shaped 100V line PA horn speakers ideal for general purpose and standard industrial installations. All models are moulded from durable ABS in an ivory colour and fitted with a high performance 100V line matching transformer and 350mm of 2 core double insulated connecting cable.

- Rotary volume tapping switch
- Adjustable steel mounting bracket
- 100V volume tapings and 8 Ohm option

	952.255UK	952.256UK
Power rms	15W	30W
Frequency response	500Hz - 7kHz	350Hz - 5kHz
SPL @ 1W/1m	100dB	108dB
Impedance	670, 1.3k, 2.6k Ohms	330, 670, 1k, 2k, 3.3k, 10k Ohms
Tappings	15W, 7.5W, 3.75W and 8 Ohms	30W, 15W, 10W, 5W, 3W, 1W and 8 Ohms
Dimensions	220 x 158 x 233mm	236 x 205 x 185mm
Weight	1.4kg	1.8kg