



17W

VT-17 17W FULL ROUND DOME LIGHT(EMERGENCY BATTERY) WITH SAMSUNG CHIP COLORCODE:4000K

Lumens 1400	Beam Angle 120	Dimensions Ø320x100mm
-----------------------	--------------------------	---------------------------------

Day White
SKU:806

3 YEARS
WARRANTY



SENSOR
COMPATIBLE



Technical Information

Watts:	17	Body Type:	PC
Lumens:	1400	Long life:	30,000 Hours
Shape:	Round	LED Chip Type:	SMD-Samsung Chip
Beam Angle:	120	IP Rating:	IP65
Battery Charging Current:	60mA	Dimmable:	No
Battery Discharging Current:	200mA	Warranty (Years):	3
Emergency Standby Watts:	>1.5	CRI:	>80
Battery Type:	Ni-CD,9.6V,1.0Ah	Operation Temperature:	-20°C to +45°C
Working Time:	>3 Hours	Input Power:	AC:200-240V,50/60Hz
Emergency Operation Time:	>3 Hours	Sensor Compatibility:	Yes
Unit Color:	White		

Features

- ✓ Premium quality LEDs with reliable lifetime
- ✓ Efficient thermal management technology
- ✓ 100% PC for Endurance/Durability
- ✓ Maintained operation suitable for long working hours
- ✓ High Power LED Samsung Chip
- ✓ Range of Dome Lights for Elegance-Ambience-Utility-Security-Weatherproof
- ✓ Constant current LED Driver for Instant start and consistent operation
- ✓ Complies with LM-80
- ✓ Applications - Office, Art Gallery, Display Case, Accent Lighting etc.

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.43
Unit CBM	0.011979

Listing Details

EAN Code	3800157636773
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	100

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES