


Cable-sensor

Type
K5RS
Issue of 11/18

Sensor

1 x Pt 100 F0,3 (old cl. B) DIN EN 60751
2-, 3- or 4-wire-circuit



Protective tube material

1.4571
Brass

Installment length

30 mm
100 mm
200 mm

Protective tube diameter

∅ 6 mm

Thread

G1/4A
1/4NPT
G1/2A
1/2NPT

Cable


PVCPVC 4x0,14	(105°C)
TeSi 2x0,34 or 3x0,34	(200°C)
TeTe 4x0,14	(260°C)
GIGIV 2x0,34 or 3x0,22	(400°C)

Cable length

2500 mm

Order Example

K5-E-2L-200-100-G1/4A



Subject to change without notice

D- 98716 Geraberg, Gewerbepark 6

Tel: +49 (0) 3677 / 7956-0 // Fax: +49 (0) 3677 / 795 625

E-Mail: info@electrotherm.de

Internet: www.electrotherm.de