

Uni-Dicht-Verschraubung Pg 11, 5-8mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5080
Specification	Uni-Dicht-Verschraubung Pg 11, 5-8mm
HARTING eCatalogue	https://b2b.harting.com/09000005080

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	20
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 11
Clamping range	5 ... 8 mm

Material properties

Material (cable glands)	Metal
Colour (accessories)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes



Pushing Performance

Material properties

California Proposition 65 substances	Nickel
	Lead

Commercial data

Packaging size	10
Net weight	6.8 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09000005080](#)